

SVN311

Impulse 1NO Pushbutton



Main electrical features

Rated operational voltage Ue	230 V
Frequency	50;60 Hz
Rated current	16 A

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	0 W
---------------------------	-----

Capacity

Number of modules	1
-------------------	---

Technical characteristics SVN311

Materials

Colour not applicable

Installation, mounting

Tightening torque 1,7Nm

Connection

Connection cross-sect. flexible conductor 0,75 ; 6mm²

Connection cross-sect. rigid cable 0,75 ; 10mm²

Type of connection with screw

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Storage temperature -40/80 °C

Temperature

Operating temperature -20/50 °C
