

# SVN332

## Latching 2NO Pushbutton

### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50;60 Hz
Rated current	16 A

### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

### Power

Total power loss under IN	0 W
---------------------------	-----

### Endurance

Electric endurance in number of cycles	15000
--	-------

Number of mechanical operations	15000
Capacity	
Number of modules	1
Materials	
Colour	not applicable
Installation, mounting	
Tightening torque	1,7Nm
Connection	
Connection cross-sect. flexible conductor	0,75 ; 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 ; 10mm <sup>2</sup>
Type of connection	with screw
Equipment	
Can be accessorized	No
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Use conditions	
Storage temperature	-40/80 °C
Temperature	
Operating temperature	-20/50 °C