

SVN422

Impulse 1NC Pushbutton + red Indicator light 230VAC



- Main electrical features
 - Rated operational voltage U_e
230 V
 - Frequency
50;60 Hz
 - Rated current
16 A
- Voltage
 - Rated insulation voltage
250 V
 - Rated impulse withstand voltage
4000 V
- Dimensions
 - Depth of installed product
66 mm
 - Height of installed product
83 mm
 - Width of installed product
17.5 mm
- Power
 - Total power loss under IN
0.8 W
- Endurance
 - Electric endurance in number of cycles
15000
 - Number of mechanical operations
15000

- Capacity
 - Number of modules
1
- Materials
 - Colour
red
- Lighting control
 - Type of lamp
LED
- Installation, mounting
 - Tightening torque
1,7Nm
- Connection
 - Connection cross-sect. flexible conductor
0,75 ; 6mm²
 - Connection cross-sect. rigid cable
0,75 ; 10mm²
 - Type of connection
with screw
- Equipment
 - Can be accessorized
No
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-20/50 °C