

# EC110

## 1 Phase kWhmeter 32A without pulsed output



- Architecture
  - Type of pole  
1P+N
  - Fixing mode  
Din-Rail
- Main electrical features
  - Frequency  
50/60 Hz
- Dimensions
  - Depth of installed product  
58 mm
  - Height of installed product  
85 mm
  - Width of installed product  
53 mm
- Power
  - Power consumed  
17.5 VA
  - Total power loss under IN  
2 W
- Capacity
  - Number of modules  
3
- Power supply
  - Supply voltage  
230 V
- Installation, mounting

- Mounting type  
din-Rail
- Connection
  - Connection cross-sect. flexible conductor  
1 / 6mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 / 10mm<sup>2</sup>
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-20/70 °C
- Temperature
  - Operating temperature  
-5/45 °C