

# TYD450

Display multi-energy consumption KNX, RT2012



- Architecture
  - Fixing mode  
flush-mounting/surface-mounting/section make
- Main electrical features
  - Frequency  
50/60 Hz
- Dimensions
  - Height of installed product  
151 mm
  - Length  
91 mm
  - Width of installed product  
23 mm
- Power
  - Power consumed  
10 W
- Power supply
  - Supply voltage  
30 V DC
- Installation, mounting
  - Mounting type  
surface
- Connection
  - Connection cross-sect. rigid cable  
0,5mm<sup>2</sup>
- Safety
  - Protection index IP

IP30

- Use conditions
  - Storage temperature  
-20/70 °C
- Temperature
  - Operating temperature  
0/45 °C