

# EC152

1Ph Kwhmeter direct 63A double tarif



- Architecture
  - Number of poles  
1 P
  - Type of pole  
1P+N
  - Fixing mode  
DIN rail type O (symmetrical)
- Main electrical features
  - Frequency  
50/60 Hz
  - Rated current  
63 A
- Voltage
  - Rated insulation voltage  
4 kV
- Dimensions
  - Height of installed product  
90 mm
  - Width of installed product  
52.5 mm
- Power
  - Power consumed  
1.3 VA
  - Total power loss under IN  
0.2 W
- Measurement
  - Type of measuring instrument

electronical

- Capacity
  - Number of modules  
3
- Power supply
  - Supply voltage  
230 V +/- 15%
- Connection
  - Connection cross-sect. flexible conductor  
1 / 16mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 / 16mm<sup>2</sup>
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-25/70 °C
- Temperature
  - Operating temperature  
-10/55 °C