

ES430A

Override contactor 25A 4NC 230V



- Main electrical features
 - Frequency
50/60 Hz
- Voltage
 - Rated insulation voltage
400 V
 - Rated impulse withstand voltage
4 kV
- Electric current
 - Acceptable current rating with AC1
20 A
- Dimensions
 - Depth of installed product
61 mm
 - Height of installed product
85 mm
 - Width of installed product
35 mm
- Power
 - Total power loss under IN
4.8 W
 - Power dissipation per coil
0.24 W
- Endurance
 - Electric endurance in number of cycles
30000
 - Number of mechanical operations

1000000

- Capacity
 - Number of modules
2
- Fluorescent bulbs control
 - Max. power with fluorescent parallel lamps
1000 VA
 - Max. power fluo. duo lamp comp. series
1000VA
- Incandescent bulbs control
 - Max. power with incandescent lamps
2500 W
- Connection
 - Connection cross-sect. flexible conductor
1 / 6mm²
 - Connection cross-sect. rigid cable
1,5 / 10mm²
 - Type of connection
with screw
 - Number of contacts
4
 - Type of contacts
4NC
- Equipment
 - Can be accessorized
No
- Standards
 - European directive WEEE
not concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-10/50 °C