

WMGS22RPSB

20A 2 Way Retractive Switch Polished Steel Black Insert



- Configuration
 - Switch mode
2pole
- Main electrical features
 - Rated current
20 A
- Dimensions
 - Depth
25 mm
 - Height
59 mm
 - Width
25 mm
- Frequency
 - Frequency
50;60 Hz
- Materials
 - Colour
silver optics
 - Material
stainless steel
- Installation, mounting
 - Imprint
with clear terminal markings
- Equipment
 - Lighting
without lighting (cannot be illuminated)

- Use conditions
 - Insert
insert, black
- Identification
 - Designation syntax: Core designation/function
Switch