

WMGSDP2/EF

20A 1 Way Double Pole Switch Marked 'EXTRACT FAN'

Configuration

Switch mode	2pole
-------------	-------

Main electrical features

Rated current	20 A
---------------	------

Dimensions

Depth	24 mm
-------	-------

Height	59 mm
--------	-------

Width	25 mm
-------	-------

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	white
--------	-------

Material	Urea-formaldehyde
----------	-------------------

Installation, mounting

Imprint with clear terminal markings

Equipment

Lighting without lighting (cannot be illuminated)

Use conditions

Insert insert white

Identification

Designation syntax: Core designation/function Switch
