

ES240

Contactor 40A 2NO 230V

:hager

- Main electrical features
 - Frequency
50/60 Hz
- Voltage
 - Rated insulation voltage
400 V
 - Rated impulse withstand voltage
4 kV
- Electric current
 - Acceptable current rating with AC1
40 A
- Dimensions
 - Depth of installed product
58 mm
 - Height of installed product
85 mm
 - Width of installed product
52.5 mm
- Power
 - Contact rating with 230 V in AC1
8500 W
 - Total power loss under IN
7.1 W
 - Power dissipation per coil
0.67 W
- Endurance
 - Electric endurance in number of cycles

- 30000
 - Number of mechanical operations
1000000
- Capacity
 - Number of modules
3
- Fluorescent bulbs control
 - Max. power with fluorescent parallel lamps
1200 VA
 - Max. power fluo. duo lamp comp. series
1300VA
- Incandescent bulbs control
 - Max. power with incandescent lamps
4000 W
- Connection
 - Connection cross-sect. flexible conductor
4 / 16mm²
 - Connection cross-sect. rigid cable
4 /25mm²
 - Type of connection
with screw
 - Number of contacts
2
 - Type of contacts
2NO
- Equipment
 - Can be accessorized
No
- Standards
 - European directive WEEE
not concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/80 °C
- Temperature
 - Operating temperature
-10/50 °C