

WMGSDP2/HTG

20A 1 Way Double Pole Switch Marked 'HEATING'



More Information

Unit	PCE
EAN	5015652260110
Sales status	3C
Depth	24 mm
Designation syntax: Core designation/function	Switch
Designation syntax: variant	20 A
Height	59 mm
Insertion depth	13.1 mm
Colour	white
Material	Urea-formaldehyde
Rated current	20 A
Appliance switch type	No
Imprint	with clear terminal markings
Insert	insert white
Labelling	with labelling
Lighting	without lighting (cannot be illuminated)

Push-buttons	No
Switch mode	2pole
Width	25 mm
