

WMGSDP2B/HD

20A 1 Way Double Pole Switch Marked 'HOT DRAWER' Black

Configuration

Switch mode	2pole
-------------	-------

Main electrical features

Rated current	20 A
---------------	------

Dimensions

Depth	25 mm
-------	-------

Height	59 mm
--------	-------

Width	25 mm
-------	-------

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	black
--------	-------

Material	Urea-formaldehyde
----------	-------------------

Installation, mounting

Imprint	with clear terminal markings
Equipment	
Lighting	without lighting (cannot be illuminated)
Use conditions	
Insert	insert, black
Identification	
Designation syntax: Core designation/function Switch	