

# WMGSDP2NB/HB

20A 1 Way Double Pole Switch with LED Indicator Marked 'HOB' Black

## Configuration

Switch mode	2pole
-------------	-------

## Main electrical features

Rated current	20 A
---------------	------

## Dimensions

Depth	25 mm
-------	-------

Height	59 mm
--------	-------

Width	25 mm
-------	-------

## Frequency

Frequency	50;60 Hz
-----------	----------

## Materials

Colour	white
--------	-------

Material	Urea-formaldehyde
----------	-------------------

## Installation, mounting

Imprint with clear terminal markings

---

Equipment

Lighting with control LED for ON

---

Use conditions

Insert insert, black

---

Identification

Designation syntax: Core designation/function Switch

---