

WRDP84FOBSB

20A Double Pole Switch with Flex Outlet Brushed Steel Black Insert

Configuration

Switch mode	2pole
-------------	-------

Dimensions

Depth	32.8 mm
Height	86 mm
Width	86 mm

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	stainless steel optics
Material	stainless steel

Installation, mounting

Imprint	with clear terminal markings
---------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
Equipment	
Lighting	without lighting (cannot be illuminated)
Use conditions	
Insert	insert, black
Identification	
Designation syntax: Core designation/function	Switch