

WRDP84NPSB

20A Double Pole Switch with LED Indicator Polished Steel Black Insert

Configuration

Switch mode	2pole
-------------	-------

Dimensions

Depth	32.8 mm
Height	86 mm
Width	86 mm

Frequency

Frequency	50;60 Hz
-----------	----------

Materials

Colour	silver optics
Material	stainless steel

Installation, mounting

Imprint	with clear terminal markings
---------	------------------------------

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting with control LED for ON

Use conditions

Insert insert, black

Identification

Designation syntax: Core designation/function Switch
