

KB190B

Insulated busbar 1P 100A prong 20mm² 57M



- Architecture
 - Number of poles
1 P
- Main electrical features
 - Rated current
100 A
- Voltage
 - Max operating voltage
230 V
 - Rated impulse withstand voltage
4 kV
- Dimensions
 - Length
1000 mm
- Capacity
 - Number of modules
57
- Materials
 - Colour
stone grey
- Connection
 - Connection cross-sect. rigid cable
20mm²
 - Type of connection
with screw
- Standards
 - European directive WEEE

concerned