

# KB280B

**Insulated busbar 2P 80A prong 16mm<sup>2</sup> 57M**

## Architecture

Number of poles 2 P

## Main electrical features

Rated current 80 A

## Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

## Dimensions

Length 1000 mm

## Capacity

Number of modules 57

## Materials

Colour stone grey

## Connection

Connection cross-sect. rigid cable 16mm<sup>2</sup>

---

Type of connection                      with screw

---

Standards

European directive WEEE              concerned

---