

# KB363C

**Insulated busbar 3P 63A prong 10mm<sup>2</sup> 24M**

## Architecture

Number of poles 3 P

## Main electrical features

Rated current 63 A

## Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

## Dimensions

Length 420 mm

## Capacity

Number of modules 24

## Materials

Colour stone grey

## Connection

Connection cross-sect. rigid cable 10mm<sup>2</sup>

---

Type of connection                      with screw

---

Standards

European directive WEEE              concerned

---