



Current transformer 250 / 5A

Technical Characteristics

Frequency	50/60 Hz
Depth of installed product	60 mm
Height of installed product	50 mm
Width of installed product	56 mm
Height of opening	30 mm
Number of modules	3.5
Connection cross-sect. flexible conductor	1,5 / 4mm ²
Connection cross-sect. rigid cable	2,5 / 6mm ²
Type of connection	screw
Protection index IP	IP20
Operating temperature	-25 °C 50 °C