

WRDS4BS

4 Gang Dimmer Switch 250W Brushed Steel

Voltage

Operating voltage 240 V AC

Frequency

Frequency 50;60 Hz

Materials

Material stainless steel

Connection

Type of load inductive

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Dimming principle phase cut-on
