

Product data sheet

EEK515P

:hager



Pluggable PIR Occupancy Sensor 5 meter lead

Technical Characteristics

Fixing mode	flush-mounting
Frequency	50/60 Hz
Halogen switching capacity 230V	2300 W
Max. power with fluo uncompensated lamps	1000 W
Incandescent bulb power	2300 W
Breaking capacity	16A 250V AC1
Supply voltage	230 V +10% / -15%
Detection angle	360 °
Colour	white
Brightness measurement range	5 Lux 1000 Lux
Maximum Mounting Height	3.5 m
Time delayed range	1min to 1h
Remote controllable	EEK001, EEK002
Protection index IP	IP41
Protection class	isol.class II