

# EC100

## Hours counter



### Architecture

Fixing mode	Din-Rail
-------------	----------

### Main electrical features

Frequency	50 Hz
-----------	-------

### Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	35 mm
----------------------------	-------

### Power

Total power loss under IN	1.5 W
---------------------------	-------

### Capacity

Number of modules	2
-------------------	---

### Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

---

Installation, mounting

Mounting type	din-Rail
---------------	----------

---

Connection

Connection cross-sect. flexible conductor 1 ; 6mm <sup>2</sup>	
--	--

---

Connection cross-sect. rigid cable	1,5 ; 10mm <sup>2</sup>
------------------------------------	-------------------------

---

Type of connection	with screw
--------------------	------------

---

Safety

Protection index IP	IP20
---------------------	------

---

Use conditions

Storage temperature	-20/60 °C
---------------------	-----------

---

Temperature

Operating temperature	-10/45 °C
-----------------------	-----------

---