

# PCR2000/1.0LSF/4

PCR2000 c/w 3 Core 1.00mm<sup>2</sup> 4m LSOH Lead

## Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Rated current	6 A

## Materials

Colour	pure white
--------	------------

## Connection

Cable End	Prepared - end of barrel closed
-----------	---------------------------------

## Cable

Conductor Size	1 mm <sup>2</sup>
Cable Material	Low Smoke Zero Halogen
Cable length	4000 mm

## Equipment

Number of terminations -sockets	4
Number of terminations -plugs	3
Contact Material	Phosphor Bronze

Technical characteristics PCR2000/1-0LSF4-A

---

Use

Mechanical Load	5 Kg maximum
-----------------	--------------

---

Safety

Inflammability	UL 94 V0
----------------	----------

---

Identification

Application, usage	Light control
--------------------	---------------

---