

# PCR2000/LSF/1.0

PCR2000 c/w 3 Core 0.75mm<sup>2</sup> 1m LSOH Lead



## Main electrical features

Rated operational voltage U <sub>e</sub>	207 / 230 / 253 V
Rated current	6 A

## Materials

Colour	pure white
--------	------------

## Connection

Cable End	Prepared - end of barrel closed
-----------	---------------------------------

## Cable

Conductor Size	0.75 mm <sup>2</sup>
Cable Material	Low Smoke Zero Halogen

## Equipment

Number of terminations -sockets	4
Number of terminations -plugs	3
Contact Material	Phosphor Bronze

---

Use

Mechanical Load	5 Kg maximum
-----------------	--------------

---

Safety

Inflammability	UL 94 V0
----------------	----------

---

Identification

Application, usage	Light control
--------------------	---------------

---