

JK304H

100A 4 Way A Board + 100A 30mA RCD

Architecture

Fixing mode surface-mounting

Main electrical features

Rated current 100 A

Dimensions

Depth of installed product 125 mm

Height of installed product 236 mm

Width of installed product 254 mm

Cover, door

Type of door closing Quarter turn lock

Interlockable Yes

Materials

Colour RAL 7035

Colour beige

Material Steel

Technical characteristics JK304H1

Equipment

Can be accessorized No

Standards

European directive WEEE concerned

Safety

Protection index IP IP2XC

Protection class Protection class III
