

JK404H

100A 4 Way A Board + 63A 30mA RCD



More Information

Unit	PCE
EAN	3250610433164
Sales status	3C
Rated current	100 A
Height of installed product	236 mm
Transparent cover or door	No
Protection index IP	IP2XC
Type of door closing	Quarter turn lock
Number of earth leakage switches 300 mA 0	
Number of poles of the main switch	2
Can be accessorized	No
Protection class	isol.class I
Depth of installed product	125 mm
Interlockable	Yes
European directive WEEE	concerned
Width of installed product	254 mm

Number of RCCB in enclosure	1
Type of protection devices	Miniature- ; earth leakage circuit breaker
Width in division units	4
Colour	beige
Number of accessible phases	1
Material	Steel
Fixing mode	surface-mounting