

VM12020

Consumer unit, Design 30, dual row, 20+20way, 100A, switch disconnecter incomer

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	100 A
---------------	-------

Dimensions

Depth of installed product	105 mm
----------------------------	--------

Height of installed product	480 mm
-----------------------------	--------

Width of installed product	471 mm
----------------------------	--------

Capacity

Number of modules	40
-------------------	----

Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

Materials

RAL colour number	9010
-------------------	------

Material	Steel
----------	-------

Equipment

Number of rows	2
----------------	---

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------