

VM24HK

Consumer unit, Design 30, 2way, 40A, garage board, RCCB, 32A MCB and 6A MCB, KO



Architecture

Fixing mode surface-mounting

Main electrical features

Rated current 40 A

Dimensions

Depth of installed product 102 mm

Height of installed product 240 mm

Width of installed product 149 mm

Capacity

Number of modules 2

Cover, door

Type of door closing non keylock

Interlockable Yes

Materials

RAL colour number	9010
-------------------	------

Material	Steel
----------	-------

Equipment

Number of rows	1
----------------	---

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------