

# VM310HK

Consumer unit, Design30, 10way, 100A, 30mA, RCCB incomer, KO

## Architecture

Fixing mode surface-mounting

## Main electrical features

Rated current 100 A

## Dimensions

Depth of installed product 102 mm

Height of installed product 240 mm

Width of installed product 292 mm

## Capacity

Number of modules 10

## Cover, door

Interlockable Yes

## Materials

RAL colour number 7035

---

Material	Steel
----------	-------

---

Equipment

Number of rows	1
----------------	---

---

Can be accessorized	No
---------------------	----

---

Standards

European directive WEEE	concerned
-------------------------	-----------

---

Safety

Protection index IP	IP2XC
---------------------	-------

---