

# VM946HK

Dual Row 4+6 Way 100A Switch 2\*100A 30mA RCCB with Knockouts



- Main electrical features
  - Rated current  
100 A
- Dimensions
  - Depth of installed product  
105 mm
  - Height of installed product  
480 mm
  - Width of installed product  
220 mm
- Capacity
  - Number of modules  
10
- Cover, door
  - Type of door closing  
non keylock
  - Interlockable  
No
- Materials
  - RAL colour number  
9010
- Equipment
  - Number of rows  
2
  - Can be accessorized  
No
- Standards

- European directive WEEE concerned
- Safety
  - Protection index IP IP2XC