

# VM9651K

Consumer unit, Design30, 12way, multi tariff 6+5+1, 1\*100A Sw, 1\*63A KO



## Architecture

Fixing mode surface-mounting

## Main electrical features

Rated current 100 A

## Dimensions

Depth of installed product 102 mm

Height of installed product 240 mm

Width of installed product 400 mm

## Capacity

Number of modules 12

## Cover, door

Type of door closing non keylock

Interlockable Yes

## Materials

RAL colour number	9010
-------------------	------

Material	Steel
----------	-------

Equipment

Number of rows	1
----------------	---

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------