

VM9662

14 Way 6+6+2 100A Switch 3*100A 30mA RCCB

:hager

- Main electrical features
 - Rated current
100 A
- Dimensions
 - Depth of installed product
102 mm
 - Height of installed product
240 mm
 - Width of installed product
471 mm
- Capacity
 - Number of modules
14
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
No
- Materials
 - RAL colour number
9010
- Equipment
 - Number of rows
1
 - Can be accessorized
No
- Standards

- European directive WEEE concerned
- Safety
 - Protection index IP IP2XC