

VM966HK

12 Way 6+6 100A Switch 2*100A 30mA RCCB with Knockouts



Main electrical features

Rated current	100 A
---------------	-------

Dimensions

Depth of installed product	102 mm
----------------------------	--------

Height of installed product	240 mm
-----------------------------	--------

Width of installed product	400 mm
----------------------------	--------

Capacity

Number of modules	12
-------------------	----

Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

Materials

RAL colour number	9010
-------------------	------

Equipment

Technical characteristics VM966HK

Number of rows	1
----------------	---

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------
