

VML610CUSPD

Design 10 , 10 way Configureable HI 63A Sw 2*63A 30mA RCCB Type A SPD

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	100 mm
----------------------------	--------

Height of installed product	246 mm
-----------------------------	--------

Width of installed product	406 mm
----------------------------	--------

Cover, door

Number of keylock of the door	0
-------------------------------	---

Interlockable	No
---------------	----

Materials

Colour	pure white
--------	------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Technical characteristics VML610CUSPD

RAL colour number	9010
Material	Steel
Equipment	
Number of rows	1
Can be accessorized	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP2XC