

EC154M

1Ph Kwhmeter direct 63A with MID approval



- Architecture
 - Number of poles
1 P
 - Type of pole
1P+N
 - Fixing mode
DIN rail type O (symmetrical)
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
63 A
- Voltage
 - Rated insulation voltage
6 kV
- Dimensions
 - Height of installed product
90 mm
 - Width of installed product
52.5 mm
- Power
 - Power consumed
1.3 VA
 - Total power loss under IN
0.2 W
- Measurement
 - Type of measuring instrument

electronical

- Capacity
 - Number of modules
3
- Power supply
 - Supply voltage
230 V +/- 15%
- Connection
 - Connection cross-sect. flexible conductor
1 / 16mm²
 - Connection cross-sect. rigid cable
1,5 / 16mm²
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-20/70 °C
- Temperature
 - Operating temperature
-10/55 °C