



### Magnetic MCB 3P 25kA 1.60A 400V Zubehörmöglich. Anzeige IEC 947-2

#### Technical Characteristics

Neutral position	not applicable
Number of poles	3 P
Type of pole	3 P
Fixing mode	DIN rail type O (symmetrical)
Curve	Mag
Rated operational voltage $U_e$	415 V
Rated current	1.6 A
Type of supply voltage	AC
Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Rated service breaking capacity $I_{cs}$ under 400V AC according IEC 60947-2	10 kA
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm
Total power loss under IN	2.5 W
Number of modules	3
Tightening torque	2,8Nm
Can be accessorized	Yes
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP20