

MMN220

Magnetic MCB 2P 25kA 20A 400V Zubehörmöglich. Anzeige IEC 947-2



- Architecture
 - Neutral position
not applicable
 - Number of poles
2 P
 - Type of pole
2 P
 - Fixing mode
DIN rail type O (symmetrical)
 - Curve
Mag
- Main electrical features
 - Rated current
20 A
 - Type of supply voltage
AC
- Voltage
 - Rated insulation voltage
500 V
 - Rated impulse withstand voltage
6000 V
- Electric current
 - Rated service breaking capacity I_{cs} under 400V AC according IEC 60947-2
10 kA
- Dimensions
 - Depth of installed product
70 mm

- Height of installed product
83 mm
- Width of installed product
35 mm
- Power
 - Total power loss under IN
4.6 W
- Capacity
 - Number of modules
2
- Installation, mounting
 - Tightening torque
2,8Nm
- Equipment
 - Can be accessorized
Yes
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/70 °C