

# VML914CUSPD

Design 10 , 14 way Configureable HI 100A Sw 2\*100A 30mA RCCB Type A SPD

## Architecture

Fixing mode	surface-mounting
-------------	------------------

## Main electrical features

Rated current	100 A
---------------	-------

## Dimensions

Depth of installed product	100 mm
----------------------------	--------

Height of installed product	246 mm
-----------------------------	--------

Width of installed product	478 mm
----------------------------	--------

## Cover, door

Number of keylock of the door	0
-------------------------------	---

Interlockable	No
---------------	----

## Materials

Colour	pure white
--------	------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Technical characteristics VML914CUSPD

RAL colour number	9010
Material	Steel
Equipment	
Number of rows	1
Can be accessorized	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP2XC