



Switch h1000 4P 800A

Technical Characteristics

Neutral position	left
Number of poles	4 P
Type of pole	4 P
Rated operational voltage Ue	690 V 220 V
Frequency	50/60 Hz
Rated current	800 A
Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
Total power loss under IN	148.8 W
Electric endurance in number of cycles	4500
Number of mechanical operations	15000
Interlockable	Yes
Tightening torque	65Nm
Connection cross-sect. flexible conductor	2x240mm ²
Connection cross-sect. rigid cable	2x240mm ²
Type of connection	Terminal
Can be accessorized	No
Standard text	IEC 60947-3
European directive WEEE	concerned
Protection index IP	IP4X
Operating temperature	70 °C -25 °C