

HCD400H

Switch h630 3P 400A



- Architecture
 - Neutral position without neutral
 - Number of poles 3 P
 - Type of pole 3 P
- Main electrical features
 - Frequency 50/60 Hz
 - Rated current 400 A
- Voltage
 - Rated insulation voltage 800 V
 - Rated impulse withstand voltage 8000 V
- Power
 - Total power loss under IN 62.4 W
- Endurance
 - Electric endurance in number of cycles 4500
 - Number of mechanical operations 15000
- Cover, door
 - Interlockable

Yes

- Installation, mounting
 - Tightening torque
22Nm
- Connection
 - Connection cross-sect. flexible conductor
35 / 240mm²
 - Connection cross-sect. rigid cable
35 / 240mm²
 - Type of connection
Terminal
- Equipment
 - Can be accessorized
No
- Standards
 - Standard text
IEC 60947-3
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP4X
- Use conditions
 - Storage temperature
-35/70 °C
- Temperature
 - Operating temperature
-25/70 °C