

JG27BR

4P 63A EARTH LEAKAGE ENCLOSED MCCB

:hager

- Architecture
 - Fixing mode
surface-mounting
- Main electrical features
 - Rated current
63 A
- Dimensions
 - Depth of installed product
106 mm
 - Height of installed product
420 mm
 - Width of installed product
300 mm
- Cover, door
 - Type of door closing
non keylock
 - Interlockable
No
- Materials
 - Colour
RAL 7035
 - Material
Steel
- Equipment
 - Can be accessorized
No
- Standards

- European directive WEEE concerned
- Safety
 - Protection index IP
IP3X
 - Protection class
Protection class III