



13A 2 Gang Double Pole Switched Socket Polished Steel White Insert

Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220 V AC 230 V AC
Rated current	13 A
Rated current	13 A
Depth	29 mm
Height	86 mm
Width	146 mm
Cover	Full cover plate
Colour	silver optics
Material	stainless steel
Surface appearance	glossy
Type of surface treatment	Other
Colour syntax: Colour	silver
Imprint	without imprint
Type of connection	screw
Wiring	with double earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Insert	insert white
Designation syntax: Core designation/function	socket outlet