

# JG43BS

**Enclosed Non-Auto MCCB 4-Pole, 250A, 25kA**

## Architecture

Fixing mode	surface-mounting
-------------	------------------

## Main electrical features

Rated current	250 A
---------------	-------

## Dimensions

Depth of installed product	135 mm
----------------------------	--------

Height of installed product	660 mm
-----------------------------	--------

Width of installed product	260 mm
----------------------------	--------

## Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

## Materials

Colour	RAL 7035
--------	----------

Material	Steel
----------	-------

---

Equipment

Can be accessorized      No

---

Standards

European directive WEEE    concerned

---

Safety

Protection index IP      IP3X

---

Protection class      Protection class III

---