



### 13A 2 Gang Double Pole Switched Socket Brushed Steel White Insert

#### Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220 V AC 230 V AC
Rated current	13 A
Rated current	13 A
Depth	29 mm
Height	86 mm
Width	146 mm
Cover	Full cover plate
Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed
Colour syntax: Colour	stainless steel
Imprint	without imprint
Type of connection	screw
Wiring	with double earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Insert	insert white
Designation syntax: Core designation/function	socket outlet