

JHF80210B

800A 12 Way Panelboard 2*250A + 10*125A Plain Door

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	800 A
---------------	-------

Dimensions

Depth of installed product	220 mm
----------------------------	--------

Height of installed product	2050 mm
-----------------------------	---------

Width of installed product	900 mm
----------------------------	--------

Capacity

Number of modules	12
-------------------	----

Cover, door

Type of door closing	Quarter turn lock
----------------------	-------------------

Interlockable	No
---------------	----

Materials

RAL colour number	7035
-------------------	------

Material	Steel
----------	-------

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------
