

WFSS82BNB-USBS

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports Black Nickel Black



- Architecture
 - Fixing mode
flush-mounting
- Main electrical features
 - Nominal voltage
250 V
 - Rated current
13 A
- Dimensions
 - Depth
39.1 mm
 - Height
86 mm
 - Width
146 mm
- Frequency
 - Frequency
50/60 Hz
- Cover, door
 - Cover
Full cover plate
- Materials
 - Material
stainless steel
 - Surface appearance
matt
 - Type of surface treatment

- brushed
 - Colour syntax: Colour stainless steel
- Installation, mounting
 - Imprint with imprint
- Connection
 - Type of connection screw
- Cable
 - Wiring with double earth connection
- Scope of delivery
 - Component with 2 fixing screws M3.5 x 20 mm
- Safety
 - Protection index IP IP20
 - Protection Enhanced contact protection
- Use conditions
 - Insert insert, black
- Identification
 - Designation syntax: Core designation/function socket outlet