

WXF422N

Double socket for trunking gallery 2P+E 16A night



- Architecture
 - Type of pole
2P+T
 - Fixing mode
Wall duct
- Main electrical features
 - Nominal voltage
250 V
 - Rated current
16 A
- Dimensions
 - Depth
45 mm
 - Height
42.5 mm
 - Width
90 mm
- Frequency
 - Frequency
50/60 Hz
- Capacity
 - Number of modules
4
- Cover, door
 - Cover
Complete housing
- Materials

- RAL colour
RAL 9005 - Jet black
- RAL colour number
9005
- Material
Polycarbonate (PC)
- Surface appearance
satin finish
- Type of surface treatment
Painted
- Connection
 - Connection cross-sect. flexible conductor
1,5 / 2,5mm²
 - Connection cross-sect. rigid cable
mini 2x1 mm² - maxi 2x2,5 mm²
 - Type of connection
Quickconnect
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
 - Protection
Enhanced contact protection
- Use conditions
 - Storage temperature
-10/50 °C
- Temperature
 - Operating temperature
-10/35 °C
- Identification
 - Designation syntax: Core designation/function
Built-in double socket outlet with earthing pin 45°, SNAP IN 4.6 mm