

JK224BDFG

JK224 128 Module Side DIN Box Glazed

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	250 A
---------------	-------

Dimensions

Depth of installed product	165.5 mm
----------------------------	----------

Height of installed product	1550 mm
-----------------------------	---------

Width of installed product	465 mm
----------------------------	--------

Capacity

Number of modules	128
-------------------	-----

Cover, door

Type of door closing	Quarter turn lock
----------------------	-------------------

Door locking	with key
--------------	----------

Interlockable	No
---------------	----

Materials

Colour	beige
RAL colour	RAL 1001 - Beige
RAL colour number	7035
Material	Steel

Equipment

Number of rows	8
Can be accessorized	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP3X
Protection class	Protection class III