

JN216B

250A 16 Way 125A Outgoers Plain

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	250 A
---------------	-------

Dimensions

Depth of installed product	220 mm
----------------------------	--------

Height of installed product	1550 mm
-----------------------------	---------

Width of installed product	710 mm
----------------------------	--------

Cover, door

Type of door closing	Quarter turn lock
----------------------	-------------------

Door locking	with key
--------------	----------

Interlockable	No
---------------	----

Materials

Colour	RAL 7035
--------	----------

Colour	beige
--------	-------

Technical characteristics JN216B2

RAL colour	RAL 1001 - Beige
RAL colour number	9001
Material	Steel

Equipment

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
Protection class	Protection class III
