

Product data sheet

WRPS22BSW

:hager



10AX 2 Gang 2 Way Wall Switch Brushed Steel White Insert

Technical Characteristics

Switch mode	2 way
Frequency	50/60 Hz
Rated current	10 A
Depth	24 mm
Height	86 mm
Width	86 mm
Colour	stainless steel optics
Material	stainless steel
Imprint	with clear terminal markings
Terminal	unique patented loop terminal allows neutral looping at the switch
Component	with 2 fixing screws M3.5 x 30 mm
Lighting	without lighting (cannot be illuminated)
Standard	BS EN 60669-1
Insert	insert white